

## Lok-it! 1800/PS Brilliant

Lok-it! Power Series (PS) | HTI Short Arc Metal Halide lamps were designed as intense light sources primarily for moving head fixtures in the Entertainment marketplace.



### Areas of application

- Concert lighting
- Club and disco
- Stage and theatre
- Studio, TV and film
- Architecture & Architainment

### Product family benefits

- Lok-it! PS for concert lighting: stable performance and reliability
- Lok-it! PS Brilliant for theaters: Life-like colors and natural skin tones (CRI 95)
- Lok-it! Blue for concert lighting: Crisp white light for cutting through the other colors on stage

### Product family features

- Natural tone of light thanks to CRI as high as 90
- Compact size and short arc gap for use in smaller and brighter fixtures
- Higher luminous efficiency than standard HID lamps
- Optimized filling for uniform light emission and a reduction in green tones standard for HID-lamps
- Plug-and-play base: PGJX28 or PGJX36
- Ceramic base allows high voltage up to 35 kV
- Individual performance features, color-coded for easy identification



# Product datasheet

## Technical data

### Electrical data

Nominal wattage	1800.00 W
Nominal voltage	88.0 V
Nominal current	20.5 A
Lamp current	20.5 A

### Photometrical data

Nominal luminous flux	148000 lm
Color temperature	6000 K
Color rendering index Ra	>92

### Dimensions & weight

Diameter	28.5 mm
Length	121.0 mm
Light center length (LCL)	60.0 mm
Electrode gap cold	5.2 mm

### Lifespan

Lifespan	750 h
----------	-------

### Environmental information

<b>Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)</b>	
Date of Declaration	06-03-2024
Primary Article Identifier	4062172040518   4062172047081
Candidate List Substance 1	No declarable substances contained
Declaration No. in SCIP database	In work

## Product datasheet

---

### Safety advice

Because of their high luminance, UV radiation and high internal pressure during operation, Lok-it! lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Appropriate filters must ensure that UV radiation is reduced to an acceptable level. Mercury is released if the lamp breaks. Special safety precautions must be taken. Information on safety and handling is available on request or can be found in the leaflet included with the lamp or in the operating instructions.

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4062172040518	Lok-it! 1800/PS Brilliant	Shipping carton box 30	400 mm x 375 mm x 295 mm	44.25 dm <sup>3</sup>	3168.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

---