

XENARC NIGHT BREAKER LASER (NEXT GEN)

Brightest OSRAM xenon light



Up to 220% more brightness¹⁾, 2)

More light allows to see farther and therefore react sooner compared to the minimum legal standard



Up to 250 m long beam

For better visibility



Up to 20% whiter light¹⁾

More modern look compared to the minimum legal standard



For more customer satisfaction

3 year guarantee, refer to www.osram.com/am-guarantee for precise conditions



The most powerful xenon light from OSRAM

XENARC NIGHT BREAKER LASER is the brightest OSRAM xenon light. This powerful lamp with efficient xenon technology ensures a better visibility on the road: up to 220% more brightness compared to the minimum legal standard. More light allows to see further and therefore react sooner. Added to this is the up to 250 meter long beam and up to 20% whiter light for more modern look (compared to the minimum legal standard). Discover the pure performance of XENARC NIGHT BREAKER LASER - the most powerful xenon light from OSRAM, available in D1S, D2S, D3S and D4S. Please note: XENARC lamp change is recommended to be carried out by a professional and in pairs.¹⁾ Compared to minimum ECE R98/R99 requirements²⁾ D3S, D4S

Product family datasheet

Technical data

Product description	Product information		Electrical Data		
	Product legal advice 1	Product legal advice 2	Power input	Nominal voltage	Nominal wattage
XENARC NIGHT BREAKER LASER D1S ¹⁾	1) Compared to minimum ECE R98/R99 requirements	2) D3S, D4S	35 W	85.0 V	35 W
XENARC NIGHT BREAKER LASER D2S ¹⁾	1) Compared to minimum ECE R98/R99 requirements	2) D3S, D4S	35 W	85.0 V	35 W
XENARC NIGHT BREAKER LASER D3S ¹⁾	1) Compared to minimum ECE R98/R99 requirements	2) D3S, D4S	35 W	42.0 V	35 W
XENARC NIGHT BREAKER LASER D4S ¹⁾	1) Compared to minimum ECE R98/R99 requirements	2) D3S, D4S	35 W	42.0 V	35 W

Product description	Test voltage	Photometric Data		Physical Attributes & Dimensions	Lifetime Data
		Nominal luminous flux	Luminous flux tolerance	Diameter	Lifespan B3
XENARC NIGHT BREAKER LASER D1S ¹⁾	13.5 V	3200 lm	±15 %	9 mm	1500 hr
XENARC NIGHT BREAKER LASER D2S ¹⁾	13.5 V	3200 lm	±15 %	9 mm	1500 hr
XENARC NIGHT BREAKER LASER D3S ¹⁾	13.5 V	3200 lm	±15 %	9 mm	2000 hr
XENARC NIGHT BREAKER LASER D4S ¹⁾	13.5 V	3200 lm	±15 %	9 mm	2000 hr

Product description	Lifespan Tc	Capabilities	Certificates & standards	Environmental & Regulatory Information Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
		Technology	ECE category	Date of declaration	Primary article identifier
XENARC NIGHT BREAKER LASER D1S ¹⁾	3000 hr	HID ²⁾	D1S ³⁾	09-07-2024	4052899631281 4052899631328
XENARC NIGHT BREAKER LASER D2S ¹⁾	3000 hr	HID ²⁾	D2S ³⁾	09-07-2024	4052899631335 4052899631298
XENARC NIGHT BREAKER LASER D3S ¹⁾	3000 hr	HID ²⁾	D3S ³⁾	09-07-2024	4052899631304 4052899631342
XENARC NIGHT BREAKER LASER D4S ¹⁾	3000 hr	HID ²⁾	D4S ³⁾	09-07-2024	4052899631359 4052899631311

Product family datasheet

Product description	Declaration no. in SCIP database
XENARC NIGHT BREAKER LASER D1S ¹⁾	In work
XENARC NIGHT BREAKER LASER D2S ¹⁾	In work
XENARC NIGHT BREAKER LASER D3S ¹⁾	In work
XENARC NIGHT BREAKER LASER D4S ¹⁾	In work

¹⁾ Reduced UV emission/For projection headlights/ECE approval and DOT label
²⁾ High-intensity discharge lamp
³⁾ To be operated only with approved electronic control gear

Download Data

File	
	Movie application Installation Video Xenarc Night Breaker Laser Opel Zafira (EN)

Safety advice

XENARC lamps should be replaced by a qualified mechanic.This product must only be operated with approved electronic control gear.

Legal advice

Light output compared to the minimum ECE R98/99 requirementsThis product must only be operated with approved electronic control gearXENARC lamps should be replaced by a qualified mechanicReduced UV emission | For projection headlights | ECE approval and DOT label± 450 lm

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.